

PRODUCT INSTRUCTION SHEET

<u>REFERENCE</u> Perching Stool 507B / 507W Perching Stool (707PU)

DESCRIPTION

Practical perching stool manufactured in high Grade with a tough nylon coating. All models Have front to back struts for additional strength. The seats 13½" x 11½" (343mm x 292mm) are padded and angled for improved posture and have an option of a PVC heat sealed seat or a PU (polyurethane) seat.

TECHNICAL SPECIFICATIONS

Adjustable height (to seat top): 21" – 27" (54 – 69cm)
Width x depth 23" x 16" (58 x 41cm)
Seat size: 13" x 11" (33 x 28cm)
Back size: 10 ½" x 6" (27cm x 15cm)

USAGE REQUIREMENTS

- 1. Do not exceed recommend weight (165kg-26 Stone)
- 2. Before, during and after use, ensure that seat fixing screws are secure.
- 3. The product is not designed to be "swung on" either in a backward, sideways or forward motion. The 4 ferrules must be in contact with the ground at all times. Use on level surfaces only.
- 4. When adjusting the legs, ensure that there is no gap between horseshoe clip and frame. The clip spindle must be fully located right through the outside frame.
- 5. Clean frame with cream cleaner, upholstery with soap and water. Ensure there is no damage to frame coating and check there are no gaps on upholstery welds.



